

SeamTekTM Glasswall TQ Epoxy Wall and Ceiling Coating System




Life Science Products

124 Speer Road, Chestertown, MD 21620 www.lspinc.com | 800-638-9874 | info@lspinc.com

© 2022 Life Science Products, Inc.

Glasswall TQ Durable, Highly Abrasion and Chemical Resistant Epoxy Coating



SeamTek™ Glasswall TQ Features

- Extremely Durable
- · No amine blush-no frosting
- Color Stable
- · Decorative Wall Surface
- Superior Impact Resistance
- Excellent adhesion to concrete
- Good Workability easy to spread
- 100% solids Solvent Free
- Low VOC -Low Odor
- High Taber Resistance
- Low Flammability

SeamTek™ Glasswall TQ **General Description**

SeamTek™ GlassWall TQ is a three-component 100% solids, low-odor, low-VOC epoxy resin wall covering system. It chemically cures to form a highly abrasion-resistant wall system when high-performance interior surface finishes are 2 required. SeamTek™ Glasswall TQ is desinged to exhibit decorative characteristics, impact resistance, chemical resistance, and durability.

It has been formulated as a mortar to be a nominal 1/8" thick. This is the same resin and aggregate formulation as an epoxy quartz floor. The basic resin component (SR101) is formulated to work with several selected hardeners to serve as a highly durable matrix. The seal coat hardener (CRH405) assures outstanding chemical resistance when compared to other CR epoxy products.

SeamTek™ GlassWall TQ can be installed over masonry, poured concrete and hardboard surfaces to provide a seamless aesthetic surface. Unless otherwise specified, SeamTek™ GlassWall TQ will follow the contour(s) of the existing substrate and cannot be used as a stand-alone system to correct such problems. SeamTek™ GlassWall TQ is designed to be 1/8" thick, which is referred to as a mortar 200°F (93°C), transportation, storage and handling are less

SeamTek™ Glasswall TQ Details and **Properties**

Specific Gravity - ASTM D 70, Fisher #3-247

Pycnometer - 1.25

Weight: ASTM E 201 - 10.7 lbs./gal

Non-Volatile Content: ASTM D 1353, 18 hrs. at

200°F (93°C) - 100%

Viscosity, cps - ASTM D 1475 77°F (25°C) 8,850 cps Flash Point TCC Minimum - Seta Flash - Greater Than

2000 F (930 C)

Solvent Odor - ASTM D1296 - Extremely Low Pot Life - 20 Minutes at 720 F (220 C) & 50% R.H. Flammability - ASTM D 635 - Self-Extinguishing

Mixing:

- 1. Apply 101 epoxy primer to the substrate and seed with fine aggregate. Allow to cure.
- Basic mortar mix: SR101 and SH101 in 2:1 mix ratio as above. Mix 1 ½ quarts (three pints) of mixed liquid with 11 quarts of color quartz or 50 mesh sand. Trowel on wall @ 12 - 13 square feet per gallon of mortar mix.
- 3. Grout Coat: Mix neat resin SR101 and hardener CRH405 in a 2:1 ratio and apply at a spread rate sufficient to fill the surface porosity. Repeat in successive applications until "holidays" disappear. This may require successive days.
- Seal Coat: Mix neat resin SR101 and hardener CRH405 in a 2:1 ratio and apply at a spread rate sufficient to leave an even sealed surface.

Storage and Handling:

Because SeamTek® GlassWall TQ has a flash point above restricted.

Limitations:

SeamTek® GlassWall TQ must not be used to bridge moving cracks or joints. Non-moving cracks or joints that must be over coated require rigid repairs. Surface or air temperature must be between 65°F minimum and 75°F maximum and relative humidity below 80%. Lower temperatures will extend cure time and higher temperatures will reduce pot and work life.

Product Health and Safety Information:

Refer to container labels and Material Safety Data Sheets available from LSP for health, safety and environmental information.

If necessary, call LSP at (800) 638-9874.

Life Science Products have been in demand by these and other highly respected institutions:

Bristol Meyer Squib | Children's Mercy | Cleveland Clinic | CalTech Univ. | Dana Farber | Duke University Emory University | F.D.A. | Harvard University | M.D. Anderson | NIH | Novartis | Northwestern University Ohio State U. | Pfizer | Princeton University | Regerneron | University of North Carolina | Yale University